

# Technical Data

Part Number: X4C5000BD-W

Product Group: CCTV

Product Type: IP Bullet Camera



## **Xvision 5MP H265+ Bullet IP Camera, 2.8mm, 30m IR, PIR Sensor, Floodlight, Starlight**

<b>Model: X4C5000BD-W</b>	
Style	Bullet Camera
Weather Resistant	Yes (IP66)
Vandal Resistant	No
Mounting Type	Wall or Ceiling
Sensor	1/2.7" Megapixel CMOS Sensor
On Board Camera Functions	Automatic White Balance, Automatic Gain Control, Automatic Electronic Iris, DNR, Starlight, Backlight Compensation, Privacy, PIR Sensor, Floodlight
Resolution	5MP
Lens Type	Fixed
Lens Size	2.8mm
Viewing Angle	92°

## Technical Data

Night Vision	30m IR
Minimum Illumination	0.05 Lux
Video Compression	H265+
Video Streams	Dual Stream
Video Resolution & Frame Rates	2592x1944 - 15fps 2592x1520 - 20fps 2048x1520 - 25fps 1920x1080 - 25fps 1280x720 - 25fps
Video Bitrate	256Kbps - 8Mbps
Network Connection	RJ45 Socket (10/100)
Network Protocols Supported	TCP/IP, HTTP, DHCP, DNS, DDNS, RTP/RTSP, PPPoE, SMTP, NTP, UPnP, SNMP, HTTPS, FTP
Onvif	Yes
Power Over Ethernet (PoE)	Yes
Power Consumption	<7W
Audio Input	Yes – Built in Mic & speaker
Power Input	12V DC Socket (2.1mm)
On Board Recording	Yes – Micro SD Card (Max 128GB)
Alarm Input	No
Video Analytics	No
PIR Distance	7m (115°)
Floodlight	10m
Operating Temperature	-30 ~ 55°
Dimensions (WHD)	Ø63x138mm
Weight (kg)	0.35
Warranty	3 Year Warranty