

CyberPower

CP825LCD INTELLIGENT LCD UPS SERIES

Offers significant energy savings,
battery backup and surge protection.

A compact UPS with standby topology, the CyberPower Intelligent LCD CP825LCD provides battery backup (using simulated sine wave output) and surge protection for desktop computers, workstations, networking devices, and home entertainment systems.

During power interruptions, the CP825LCD offers reliable power protection and battery backup.

The CP825LCD comes with a three-year warranty (including coverage of batteries) and a \$225,000 Connected Equipment Guarantee.

TYPICAL APPLICATIONS

- Desktop Computers
- Home Networking/VoIP
- Personal Electronics
- Home Theater Devices

FEATURES

- 825 VA / 450 W
- Standby Topology
- Multifunction LCD Screen
- GreenPower UPS™
- ENERGY STAR® Qualified
- Full-time Surge Protection & Battery Backup
- Compact Form Factor
- RJ11/RJ45 Protection
- 8 Outlets / USB Port
- PowerPanel® Personal
- 3-Year Warranty



CP825LCD

INTELLIGENT LCD UPS SERIES

SPECIFICATIONS

GENERAL

UPS Topology	Standby
ENERGY STAR® Qualified	Yes

INPUT

Voltage	120 VAC
Frequency Range	57 – 63 Hz
Plug Type	NEMA 5-15P
Plug Style	Right Angle
Cord Length	6 ft

OUTPUT

VA	825 VA
Watts	450 W
Automatic Voltage Regulation	No
On Battery Voltage	120 VAC ± 5%
On Battery Frequency	60 Hz ± 1%
On Battery Waveform	Simulated Sine Wave
Outlet Type	NEMA 5-15R
Outlets - Total	8
Outlets - Battery & Surge Protected	4
Outlets - Surge-Only Protected	4
Outlets - Widely Spaced	4
Overload Protection	Internal Circuitry Limiting / Circuit Breaker
Transfer Time	4 ms

BATTERY

Runtime at Half Load	8 minutes
Runtime at Full Load	1 minutes
Battery Type	Sealed Lead-Acid
Battery Size	12V/8.5Ah
Battery Quantity	1
User Replaceable	Yes
Replacement Battery Cartridge	RB1280A
Replacement Battery Cartridge Quantity	1
Typical Recharge Time	8 hours



SURGE PROTECTION & FILTERING

Surge Suppression	1,030 J
Phone RJ11 / Ethernet RJ45	1-In, 1-Out (Combo)

MANAGEMENT & COMMUNICATIONS

Multifunction LCD Panel	Displays: Current/Load Level, Runtime, Battery Level, Input Voltage, Output Voltage, Battery In Use, Overload, Silent Mode, Normal Mode
HID Compliant USB Port	Yes
LED Indicators	Power On, Wiring Fault
Audible Alarms	On Battery, Low Battery, Overload
Software	PowerPanel® Personal

PHYSICAL

Form Factor	Compact
Keyhole Mounting Slots	Yes
Dimensions - W×H×D (in)	11 × 6.5 × 3.5 inches
Weight (lbs)	15.0 lbs

ENVIRONMENTAL

Operating Temperature	32 – 95 °F (0 – 35 °C)
Operating Humidity	0 – 95% (non-condensing)

CERTIFICATIONS

Safety	UL1778, cUL 107.1, FCC DOC Class B
Environmental	RoHS Compliant

WARRANTY

Product Warranty	3 Years Limited
Connected Equipment Guarantee	Lifetime
CEG Amount	\$225,000