




**SPECIFICATION
CONTROL DRAWING
Crystal Resonator**

FREQUENCY
13.560000MHz



Holder Style	3X25X06 4-Pad
Mode	Fundamental
Adjustment Tolerance	± 30 PPM at 25°C
Temperature Stability	± 30 PPM
Operating Temp. Range	-40°C to +85°C
Load Capacitance	10 pF
ESR	80 Ohm
Static Capacitance (C0)	unspecified pF
Ageing	+/-2ppm 1st year max
Marking	AEL13.56WW/YY

Amdt Date	Change Note	AEL Code
		X13M560000S041
		Issue Ref A