




**SPECIFICATION
CONTROL DRAWING
Crystal Resonator**

FREQUENCY
24.000000MHz



Holder Style
Mode
Adjustment Tolerance
Temperature Stability
Operating Temp. Range
Load Capacitance
ESR
Static Capacitance (C0)
Ageing
Marking

3X25X06 4-Pad
Fundamental
 ± 10 PPM at 25°C
 ± 10 PPM
-20°C to +70°C
18 pF
60 max Ohm
Unspecified pF
+/-5ppm first year
AEL24A
WWYY

Amdt Date	Change Note	AEL Code
		X24M000000S094
		Issue Ref
		A