




**SPECIFICATION
CONTROL DRAWING
Crystal Resonator**

**FREQUENCY
30.000000MHz**



Holder Style	3X25X06 4-Pad
Mode	Fundamental
Adjustment Tolerance	± 10PPM at 25°C
Temperature Stability	± 10 PPM
Operating Temp. Range	-20°C to +70°C
Load Capacitance	12 pF
ESR	50 Ohms Max Ohm
Static Capacitance (C0)	Unspecified pF
Ageing	+/-3ppm 1st Year Max
Marking	AEL30.00 WW/YY

Amdt Date	Change Note	AEL Code
		X30M000000S043
		Issue Ref A