

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2059570971](#)

Status: **Active**

Overview: [Micro-Lock Plus Wire-to-Board Connector System](#)

Description: 1.25mm Pitch, Micro-Lock PLUS PCB Header with Potting Capability, Single Row, Vertical, Surface Mount, Tin-Bismuth Plating, Positive Lock, 9 Circuits, Tape and Reel, Black

Documents:

[Drawing \(PDF\)](#)

[Product Specification 2045320001-PS-000 \(PDF\)](#)

[Packaging Specification 2059579200-SPK-200 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification


| | |
|-----|---------|
| CSA | LR19980 |
| UL | E29179 |

General

| | |
|----------------------|--|
| Product Family | PCB Headers |
| Series | 205957 |
| Application | Signal, Wire-to-Board |
| CURRENT-MAX-NUMERIC | 3.6 |
| Datasheet Order No | 987652-1192 |
| Overview | Micro-Lock Plus Wire-to-Board Connector System |
| PITCH-MATING-NUMERIC | 1.25 |
| Product Name | Micro-Lock PLUS |
| UPC | 191130032280 |

Physical

| | |
|--------------------------------|-----------------------|
| Breakaway | No |
| Circuits (Loaded) | 9 |
| Circuits (maximum) | 9 |
| Color - Resin | Black |
| Durability (mating cycles max) | 30 |
| First Mate / Last Break | No |
| Glow-Wire Capable | No |
| Guide to Mating Part | No |
| Keying to Mating Part | None |
| Lock to Mating Part | Yes |
| Material - Metal | Brass |
| Material - Plating Mating | Tin-Bismuth |
| Material - Plating Termination | Tin-Bismuth |
| Material - Resin | Polyamide |
| Net Weight | 364.090/mg |
| Number of Rows | 1 |
| Orientation | Vertical |
| PCB Locator | No |
| PCB Retention | Yes |
| Packaging Type | Embossed Tape on Reel |
| Pitch - Mating Interface | 1.25mm |
| Pitch - Termination Interface | 1.25mm |
| Plating min - Mating | 1.000µm |
| Polarized to Mating Part | Yes |
| Polarized to PCB | Yes |
| Robotic Placement | Vacuum Pick-Up Tape |
| Shrouded | Fully |
| Stackable | No |
| Surface Mount Compatible (SMC) | Yes |
| Temperature Range - Operating | -40° to +105°C |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[205957](#) Series

Mates With

[Micro-Lock PLUS Receptacle Housing](#)
[204532](#)

Termination Interface: Style

Surface Mount

Electrical

Current - Maximum per Contact

3.6A

Voltage - Maximum

50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Packaging Specification

2059579200-SPK-200

Product Specification

2045320001-PS-000

Sales Drawing

2059573000-SD-000

This document was generated on 09/25/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION