


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2045320801](#)
Status: **Active**
Overview: [Micro-Lock Plus Wire-to-Board Connector System](#)
Description: Micro-Lock PLUS Receptacle Housing, 1.25mm Pitch, Single Row, with Positive Lock, 8 Circuits, Low-Halogen, Black

Documents:

Drawing (PDF)	Application Specification AS-505565-001-001 (PDF)
Product Specification 2045320000-PS-000 (PDF)	Packaging Specification 2045329200-200 (PDF)
Product Specification 2045320000-PS-001 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 2045320001-PS-000 (PDF)	



Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	204532
Application	Signal, Wire-to-Board
Datasheet Order No	987652-1192
Overview	Micro-Lock Plus Wire-to-Board Connector System
Product Name	Micro-Lock PLUS
UPC	191128418355

Physical

Circuits (maximum)	8
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	154.677/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.25mm
Pitch - Termination Interface	1.25mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

Material Info

Reference - Drawing Numbers

Application Specification	AS-505565-001-001
Packaging Specification	2045329200-200
Product Specification	2045320000-PS-000, 2045320000-PS-001, 2045320001-PS-000
Sales Drawing	2045320000-SD-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[204532 Series](#)

Mates With

Micro-Lock PLUS Header [205957](#)

Use With

Micro-Lock PLUS Terminal [505431](#)