

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2034382209](#)  
**Status:** **Active**  
**Overview:** [CP Wire-to-Board and Wire-to-Wire Connector Systems](#)  
**Description:** CP-6.5 Plug Housing, 6.50mm Pitch, Dual Row, 2 Circuits, Red, Glow-Wire Capable

**Documents:**

[Drawing \(PDF\)](#) [Test Summary 2034380001-TS-000 \(PDF\)](#)  
[Product Specification 2034380001-PS-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Packaging Specification 2034380001-PK-000 \(PDF\)](#)

**General**

Product Family	Crimp Housings
Series	<a href="#">203438</a>
Application	Power, Wire-to-Wire
Datasheet Order No	987651-1601
Overview	<a href="#">CP Wire-to-Board and Wire-to-Wire Connector Systems</a>
Product Name	CP-6.5
UPC	191130083886


**Physical**

Circuits (maximum)	2
Color - Resin	Red
Gender	Plug
Glow-Wire Capable	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.882/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	6.50mm
Pitch - Termination Interface	6.50mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	2034380001-PK-000
Product Specification	2034380001-PS-000
Sales Drawing	2034380000-SD-000
Test Summary	2034380001-TS-000



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/71/2019 (16 July  
2019)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[203438 Series](#)

**Mates With**

CP-6.5 Receptacle Housing [1512072209](#)

**Use With**

CP-6.5 Terminal [205032](#) , CP-6.5 TPA  
Retainer [511430105](#)