

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2078410002](#)  
**Status:** **Active**  
**Overview:** [L1NK Connector System](#)  
**Description:** L1NK 250 Receptacle Housing, Single Row, 2 Circuits, UL 94V-0, Black

**Documents:**

<a href="#">3D Model</a>	<a href="#">Packaging Specification 2078410000-PK-000 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Test Summary 2079020000-TS-000 (PDF)</a>
<a href="#">Product Specification 2079020001-PS-000 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Application Specification 2079020001-AS-000 (PDF)</a>	

**Agency Certification**

CSA	152514
UL	E29179

**General**

Product Family	Crimp Housings
Series	<a href="#">207841</a>
Application	Power, Wire-to-Board
Datasheet Order No	987651-9951
Overview	<a href="#">L1NK Connector System</a>
Product Name	L1NK 250
UPC	191130123933


**Physical**

Circuits (maximum)	2
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.250/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

**Material Info**

**Reference - Drawing Numbers**

Application Specification	2079020001-AS-000
Packaging Specification	2078410000-PK-000
Product Specification	2079020001-PS-000
Sales Drawing	2078410004-SD-000
Test Summary	2079020000-TS-000



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/88/2018 (15  
January 2019)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[207841](#) Series

**Mates With**

L1NK 250 Header [207843](#)

**Use With**

L1NK 250 Crimp Terminals [46626](#)  
<br>L1NK 250 TPA [207845](#)