

Mini AC Clamp-On Meter

MODEL 9200-A



Applications







- Measure AC Current in lines, generators, and more!
- Perfect for professionals and DIY
- Perform all the standard measurement functions of a DMM

Features

- 3 3/4 digit, 4000 count backlit display
- AC Current up to 300A
- CAT II 300V certified
- Data hold
- 3 year limited warranty



TRIPLETT CLAMP METERS COMPARISON CHART

	Triplett's Current Gen of Meters			Triplett's Last Gen of Meters		
						
Model	9200	9305	9325	9300-A	9310-A	9320-A
Style	Mini	Compact	Full Size	Full Size	Full Size	Full Size
Ranges:						
TRMS	N	N	Y	N	N	Y
AC Current (Max Res)	300A (0.01A)	400A (0.01A)	1000A (0.1A)	1000A	1000A	1000A
DC Current (Max Res)	N	N	1000A (0.1A)	N	1000A	1000A
AC Voltage (CAT III)	N	600V	600V	600V	600V	600V
DC Voltage (CAT III)	N	600V	600V	600V	600V	600V
Resistance	N	Y	Y	Y	Y	Y
Capacitance	N	Y	Y	N	Y	Y
Temperature	N	Y	Y	N	Y	Y
Diode	N	Y	Y	Y	Y	Y
Continuity	N	Y	Y	Y	Y	Y
Frequency (60Hz Res)	N	(0.1Hz)	(0.1Hz)	N	(0.1Hz)	(0.1Hz)
Duty Cycle	N	N	Y	N	Y	Y
Autorange	Y	Y	Y	N	Y	Y
Data Hold	Y	Y	Y	Y	Y	Y
Min / Max	N	N	Y	N	N	Y
Peak, Inrush Current	N	N	N	N	N	N
Bar Graph	N	N	Y	N	N	N
Voltage Detector	N	Y	Y	N	N	N
CAT Rating (600V)	CAT II	CAT III	CAT III	CAT III	CAT III	CAT III
Rel	N	Y	Y	N	Y	Y
Features:						
Length	5.8"	7.8"	9.1"	8.63"	8.63"	8.63"
Weight	3.4 oz.	7.2 oz.	9.6 oz.	12 oz.	12 oz.	12 oz.
Housing	Plastic	Overmolded	Overmolded	Plastic	Plastic	Plastic
Max. Cable Dia.	300MCM	450MCM	500MCM	500MCM	500MCM	500MCM
Digital Display	3 3/4 Digit, 4000 Count	3 3/4 Digit, 4000 Count	3 3/4 Digit, 6000 Count	3 1/2 Digit, 2000 Count	3 3/4 Digit, 4000 Count	3 3/4 Digit, 4000 Count
Auto Power Off	Y	Y	Y	N	Y	Y
Backlit	N	Y	Y	Y	Y	Y
Warranty	3 years	3 years	3 years	3 years	3 years	3 years
Case Included	Y	Y	Y	Y	Y	Y
Battery	3V CR2032	2-AAA	1-9 Volt	1-9 Volt	1-9 Volt	1-9 Volt