

MP710066 and MP710067

DC Power Supplies

multicomp PRO



- 3-channel linear DC power supplies feature
- Low ripple/noise
- Constant voltage/current
- Over load protection
- Parallel/series
- Output on/off control



		MP710066	MP710067
Output voltage	CH1, CH2	0~32V	0~32V
	CH3	5V	5V
Output current	CH1, CH2	0~3A	0~5A
	CH3	3A	3A
Output power		207W	335W
Load regulation		CV $\leq 1 \times 10^{-4} + 3\text{mV}$, CC $\leq 2 \times 10^{-4} + 3\text{mA}$	
Ripple and noise		CV $\leq 1\text{mVrms}$; CC $\leq 3\text{mArms}$	
Output regulation resolution		CV: 100mV (typical), CC: 10mA (typical)	
Tracking bias		$5 \times 10^{-3} + 10\text{mV}$	
Reliability		MTBF(e): $\geq 2000\text{hrs}$	
Display mode		3-bit voltage and current dual display	
Features		Auto conversion of constant voltage and current with current limit protection; CH1 and CH2 master-slave tracking in series	
Power		Input voltage: 115V AC/230V AC; Frequency: 47Hz~63Hz	
Product color		White and grey	
Product net weight		8.7kg	10kg
Product size		260mm x 170mm x 315mm	
Standard accessories		Power cord, output cables	
Standard individual packing		Carton box, English manual	
Standard quantity per carton		1pcs	
Standard carton measurement		435mm x 340mm x 255mm	
Standard carton gross weight		10.5kg	12kg