

Part number

CX 02 7M



Brief description:

male insert, 2 poles, crimp connections, 70A 1000V, 8kV, 3, 2 modules, modular units series MIXO

Product description	
Model	male insert
Version	Crimp connection
Product type	for 70A male contacts
Family	MIXO series, customizable inserts
Size	1 module
N. of poles	2 poles
Technical data	
Current	70 A (A.C. and D.C.)
Voltage	1000 V
Rated impulse withstand voltage	8 kV
Pollution degree	3
Operating temperature range (min, max)	-40°C ... +125°C
IP degree of protection	IP20 without enclosure, IP65/IP66/IP68/IP69 with enclosure
Further technical details	
Characteristics according to EN 61984	70A 1000V 8kV 3; 70A 1600V 12kV 2
Insulation resistance	≥ 10 GΩ
Rated voltage according to UL/CSA	600V
UL 94 flammability rating	V-0
Weight	10,50 g

Approvals / Standards	
Reference standard	EN 61984:2009-06
Quality mark	 DNV GL, BV, EAC
Conformity	CQC, CE
General ordering information	
EAN13 code	8015747182447
Tariff number	85369095
Packaging Information	
Packaging length	180,00 mm
Packaging height	130,00 mm
Packaging width	150,00 mm
Packaging weight	0,80 kg
Packaging volume	3,51 dm ³
Packaging description	Carton box
Packaging quantity	60 Pcs
Packaging EAN code	8015747221153
Sub-packaging length	35,00 mm
Sub-packaging height	40,00 mm
Sub-packaging width	155,00 mm
Sub-packaging weight	0,13 kg
Sub-packaging volume	0,22 dm ³
Sub-packaging description	Carton tray
Sub-packaging quantity	10 Pcs
Sub-packaging EAN barcode	8015747182539

Part number

CX 02 7M



Notes

the modular inserts must be installed in suitable frames which in turn are installed in traditional housings or COB panel support
