

Part number

CGMA 10



Brief description:

100A CG contacts, silver plated, 8-10mmq, AWG 8-7

Product description

Model	male contacts
Version	Crimp contacts CLASS series
Series	100A CG contacts
Family	crimp contacts
N. of poles	1 pole

Technical data

Current	100 A
Wire cross-section	8,00 mm ² - 10,00 mm ²
AWG size	8 - 7
Contact type	silver plated

Further technical details

Weight	19,00 g
---------------	---------

Approvals / Standards

Quality mark	 DNV GL, BV, EAC
Conformity	CQC, CE

General ordering information

EAN13 code	8015747091121
Tariff number	85369095

Packaging Information

Sub-packaging length	1,00 mm
Sub-packaging height	1,00 mm
Sub-packaging width	1,00 mm
Sub-packaging weight	0,57 kg
Sub-packaging description	Plastic box
Sub-packaging quantity	30 Pcs
Sub-packaging EAN barcode	8015747091206

Part number

CGMA 10



Catalogue drawings

CGF and CGM

