

---

## SAC 2 Way Indoor UHF/DAB Amp 12dB Gain

---

- **Product code: AE5042**
  - **Specifications:**
    - **Dimensions: 68x127x45mm - Weight: 390g**
- Distribute UHF-FM/DAB signal around the home with SAC 2 inputs 2 outputs indoor distribution amplifier. With built-in IR pass for use with 'magic eyes'. LTE/4G protected. Fully shielded with F type connectors.
- Built-in IR pass for use with 'magic eyes' (not included) - Distribute signal to several TV's or Hi-fi's
  - Fully shielded with F type connectors - LTE/4G Protected
- UHF + FM/DAB Inputs - Power on, short-circuit & surge protector indicator
  - Number of outputs: 2 - Input frequency band: UHF/VHF
- Frequency range UHF: 470-790MHz - Frequency range VHF: 47-230MHz
- Output frequency range: 47-790MHz - Return path frequency: 5-25MHz
  - Gain per split: 12dB - Output level: 97dB $\mu$ V Max
    - Isolation: 22dB - Noise Figure: <3.8dB
    - Impedance: 75ohms - IR pass: yes
  - Short-circuit protection: yes - Surge protection: yes
    - Power supply: AC 220-240v 50Hz - ce certified
- Contents: 1 x Amp with power supply, 1 x Manual, 2 x screws

