



40" Full HD LED Smart TV with Wi-Fi

- 40" Smart TV with Wi-Fi
- Full HD LED Panel
- Built-in Freeview DVB-T2 HD channels
- Watch your favourite catch up and streaming entertainment apps
- 16.7 million display colours
- 4000:1 contrast ratio
- 1920 x 1080 screen resolution
- USB 2.0 - Play media files from other devices
- HDMI x 3 inputs for external devices & consoles

	EAN	5060062269222
General Feature	Model No.	C40RTS
	Panel	60Hz
	Destination Country	UK
	Screen Size	40"
	Max. Resolution	1920 x 1080
	Contrast Ratio (Typical)	5000:1
	Brightness (TYP cd/m2)	200
	Display Colors	16.7 million
	Viewing Angle H/V	178/178
	Cabinet Color	Piano Black

Reception	TV System	DVB-T, DVB-T2
------------------	-----------	---------------

Sound	Bass	Yes
	Treble	Yes
	Balance	Yes
	Sound Mode	Standard/music/movie/user
	Stereo System	N/A
	Audio Output	2 x 8W
	3D Digital Comb Filter	Yes
	3D Noise Reduction	Yes

Connectors Jack	HDMI Input	YES x 3
	RJ45	YES x 1
	Headphone	YES x 1
	15-PIN VGA + AUDIO Input	YES x 1
	RF Input	YES x 1
	Mini AV	YES x 1
	Mini YPBPR	YES x 1

Other Features	APS	DVBT
	OSD Language	English, German, Francais, Espanol, Portugese, Italian.
	PVR function	Recording standby, time-shift, EPG recording reservation
	Electronic programme guide	7 days

Power	Power Supply	AC120-230, 50-60HZ
	Operation Power Consumption	90W
	Standby Power Consumption	<0.5W

Accessories	Remote Control	YES x 1
	Power Cable	YES x 1
	Warranty	YES x 1
	Battery	1.5V (AAA) x 2

Dimension	Unit Dimension With Stand (W x D x H mm)	913.6 x 257.38 x 580.44
	Unit Dimension Without Stand (W x D x H mm)	913.6 x 84.8 x 538.43