




# Kasa Spot Pan Tilt

Indoor Security Camera



KC110



# Features



## Crystal Clear Video

Sharp and clear 1080p full-HD provides high-quality video right in the palm of your hand.

## Pan and Tilt

Swipe up, down, left and right on your phone to rotate and set the camera's point of view.

## Motion Tracking

When motion activity is detected, Kasa Spot Pan Tilt tracks and follows the subject to keep it within the camera's field of view.



## Cloud Storage Plans

Upgrade your Kasa Care subscription plan and enjoy full video recordings for up to 30 days.

## Night Vision

Even at night, the camera will detect activity 30 ft. away with Night Vision.

## Patrol Mode

Set multiple distinct viewpoints and program your pan tilt camera to keep an eye on each region at intervals of your choosing.



## Two-Way Audio

Use crisp two-way audio to communicate with nosy roommates, family or even mischievous pets.

# Specifications

## Camera

**Image Sensor:** 1/2.7"(Φ6.6)  
**Resolution:** 1080p HD  
**Night Vision:** 850 nm IR LED up to 30 ft  
**Lens:** F/NO: 2.2; Focal Length: 3.97mm  
**View Range:** 360° horizontal and 118° vertical

## Audio

**Audio Communication:** 2-way audio  
**Audio Input & Output:**  
Built-in microphone and speaker

## Video

**Video Compression:** H.264  
**Frame Rate:** 15fps  
**Video Streaming:** 1080p  
**Audio Compression:** AAC

## Activity Notifications

**Input Trigger:**  
Motion detection, Audio detection,  
Motion tracking  
**Output Notification:**  
Push notification

## Hardware

**Button:** RESET button  
**Indicator LED:** System LED  
**Adapter Input:** 100-240VAC, 50/60Hz, 0.5A  
**Adapter Output:** 5.0VDC, 2.0A  
**Dimensions (W x D x H):**  
3.2 x 3.2 x 4.4 in. (82 x 82 x 112.6 mm)

## Network

**Wireless Rate:**  
11Mbps(802.11b)  
54Mbps(802.11g)  
150Mbps(802.11n)  
**Frequency:** 2.4GHz  
**Wireless Security:** WEP, WPA/WPA2-PSK  
**Security:** 128 bit AES encryption with SSL/TLS

## System

**Regulatory Certification:**  
FCC, IC, CE  
**System Requirements:**  
iOS 10+, Android 5.0+

## Environment

**Operating Temperature:**  
0°C~40°C (32°F~104°F)  
**Storage Temperature:**  
-20°C~70°C (-4°F~158°F)  
**Operating Humidity:**  
10%~90%RH non-condensing  
**Storage Humidity:**  
5%~90%RH non-condensing

## Package Contents

Kasa Spot PanTilt  
Power Adapter  
10 ft USB Cable  
Quick Start Guide  
Mounting Screws  
Mounting Plate

