


Data sheet | Item number: 762-4104

Touch Panel 600; 25.7 cm (10.1"); 1280 x 800 pixels; 2 x USB, 2 x ETHERNET;
Web Panel





www.wago.com/762-4104



RoHS
Compliant ✓

BOMcheck.net



Item description

Hardware Configuration PIO1

- Two ETHERNET ports for connecting to field devices and the engineering tool
- Two USB ports for optional connection of a USB stick, mouse or keyboard



Data

Technical Data

Display diagonal	25.7 cm (10.1 Inches)
Display	Resistive touchscreen
Display colors	16 million colors
Graphics resolution	(1280 x 800) px
Visualization	Web server
Ethernet protocol	DHCP DNS FTP FTPS HTTP HTTPS SSH
Communication	Web browser
Operating system	Real-time Linux (with RT-Preempt patch)
Processor	ARM [®] Cortex™ A9
Main memory (RAM)	2048 MB
Internal memory (flash)	4096 MB
Type of memory card	microSD (max. 2 GB), microSDHC (max. 32 GB)
Indicators	five LEDs
Panel	Resistive touch panel, two capacitive keys, proximity sensor
Supply voltage	SELV DC 24 V (18 ... 31.2 V); mit Verpolungsschutz

Connection data

Connection technology: communication/fieldbus	Web browser: 2 x RJ-45; 2 x USB 2.0 host (type A)
---	---

Geometrical Data

Width	293 mm / 11.535 inch
Height	223 mm / 8.78 inch
Depth	58 mm / 2.283 inch

Mechanical data

Weight	1509
--------	------

Environmental Requirements

Surrounding air (operating) temperature	0 ... 55 °C
Surrounding air (storage) temperature	-20 ... 80 °C
Protection class	IP65
Note on protection class	Front side IP65, rear side IP20, per EN 60529




Relative air humidity (no condensation)	90 %
Mounting type	Clamping elements (included) or VESA mount (4 x M4x8)

Commercial data

Packaging type	BOX
Country of origin	DE
GTIN	4055143825061
Customs Tariff No.	8471410000

Approvals / Certificates**UL-Approvals**

Logo	Approval	Additional Approval Text	Certificate name
	UL Underwriters Laboratories Inc. (ORDINARY LOCATIONS)	UL 61010-2-201	E175199

Compatible products**memory card**

	Item no.: 758-879/000-3102 Memory Card SD Micro; 2 GByte	www.wago.com/758-879/000-3102
--	--	--

assembling

	Item no.: 762-9001 eDISPLAY7300T ; Clamping elements (4 pieces)	www.wago.com/762-9001
--	---	--

Downloads**Documentation****Manual**

TP 600 WAGO Touch Panel 600	1.1.0 25-Jul-2019	pdf 2.7 MB	Download
--------------------------------	----------------------	---------------	----------

System Description

Touch Panel 600, system description	pdf 727.2 kB	Download
-------------------------------------	-----------------	----------



Handling Instructions

Product family

Standard Line

Show all products from the family

Subject to changes.

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169

Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?

We are always happy to take your call at +49 (571) 887-44222.