


## SX82 Series | Double-pole switch 20A quick connection 6.3 black body, red illuminated

PRODUCT CODE: SX8211881G210093



Body colour



Marking



Actuator colour



Marking colour



Approvals




### Rating

20 (2) A / 250 VAC  
 16 (8) A / 250 VAC  
 10 (6) A / 250 VAC - 5E4  
 T125/55 °C  
 EN 61058

20 A / 125 VAC  
 16 A / 250 VAC  
 3/4 HP - 125 VAC / 250 VAC  
 T105 °C  
 UL 1054

Mechanical Life: >50,000 cycles  
 Protection degree: IP40  
 Contact opening: full disconnection > 3mm

### Panel Cut Out



L	K	J
28.2 <sup>+0.1</sup> <sub>0</sub>	22.3 <sup>+0.1</sup> <sub>0</sub>	0.7+3.5

### Dimensions (mm)

