

# 18Vx2 LAWN MOWER 38CM LXT

## DLM380Z

Cost-competitive 380mm cordless lawn mower powered by two 18V Li-ion batteries in series.  
Recommended for lawns 270-540m<sup>2</sup>

18Vx2 LAWN MOWER 38CM LXT



### TECHNICAL SPECIFICATIONS

Battery Type	Li-ion
Battery Quantity (3.0 Ah)	0
Body only machine	✓
Voltage	36 (18v x2) v
Noise sound pressure	81 dB(A)
Noise sound power	93 dB(A)
Noise K factor	3 dB(A)
Blade type	Rotary type 2 tooth
Cutting diameter	380 mm
Cutting heights	6 / 25-75 Levels/ mm
Collection box	40 litres
Maximum Output	620 w
No Load Speed	3700 rpm
Vibration K factor	1.5 m/sec <sup>2</sup>
Vibration no load	2.5 m/sec <sup>2</sup>
Net weight	14.5 - 15.0 kg

### USER BENEFITS

- Powered by two 18V Li-ion batteries in series to supply energy to the powerful 36V DC motor drive system.
- Battery capacity warning lamp.
- Soft start
- Electronic brake.
- Single lever cutting height adjustment
- No pipe across handle means easier installation and removal of grass bag.
- Grass level indicator - indicator plate will be closed if bag is full.

Link to product - [www.makitauk.com](http://www.makitauk.com)



# RELATED PRODUCTS

(Reco

## ■ OTHER