

Twin 18V Lawn Mower LXT

DLM431Z

Cordless push-type Lawn Mower designed for cutting lawn surface up to 950m²



TECHNICAL SPECIFICATIONS

Battery Type	Li-ion
Body only machine	✓
Voltage	36 (18v x2) v
Noise sound pressure	80 dB(A)
Noise sound power	93 dB(A)
Noise K factor	3 dB(A)
Blade type	Rotary type 2 tooth
Cutting diameter	430 mm
Cutting heights	13 / 20-75 Levels/ mm
Collection box	50 litres
Maximum Output	730 w
No Load Speed	3600 rpm
Vibration K factor	1.5 m/sec ²
Vibration no load	2.5 m/sec ²
Net weight	17.8 - 18.4 kg

USER BENEFITS

- Electronic current limiter for overload protection.
- Electric brake
- Soft start
- Powered by two 18V Li-ion batteries in series to supply energy to the powerful 36V DC motor drive system.
- Dual battery fuel gauge
- Single lever cutting height adjustment
- Grass box with grass level indicator
- Rubberised handle bar
- Wheels with built in ball bearing for additional durability
- Foldable handle for compact easy storage
- Low noise and vibration

[Link to product - www.makita.com](http://www.makita.com)



RELATED PRODUCTS

(Reco

■ OTHER