




# 5.08mm high power rising clamp terminal blocks

## Product overview


- 2-12 pole interlocking
- Captive screws
- Moulded in green UL94-V0 flame retardant PA
- Professional rising clamp terminals
- 0.05-3.3mm<sup>2</sup> (30-12 AWG)
- approved

CTB0709



SPECIFICATION	
Rating	20A 300V
Insulation resistance	5000M $\Omega$ /1000V
Withstand voltage	AC2000V/1min
Contact resistance	20m $\Omega$
Working temperature	-33°C to +120°C
Moulding	UL94-V0 flame retardant PA66
Pin/terminal	Tin plated brass
Rising clamp	Nickel plated brass
Screw/torque	M3 steel, nickel plated 0.4Nm
Recommended PCB hole size	$\phi$ 1.6mm

PART NO.	POLES	LENGTH
CTB0709/2	2	10.16mm
CTB0709/3	3	15.24mm
CTB0709/4	4	20.32mm
CTB0709/5	5	25.4mm
CTB0709/6	6	30.48mm
CTB0709/7	7	35.56mm
CTB0709/8	8	40.64mm
CTB0709/9	9	45.72mm
CTB0709/10	10	50.8mm
CTB0709/11	11	55.88mm
CTB0709/12	12	60.96mm



## KEY FEATURES

Professional rising clamps | High power 20A | Interlocking

