

# PCB TERMINAL BLOCKS

PCB  
TERMINAL  
BLOCKS

INTER-  
CONNECTION

FUSES &  
FUSE-  
HOLDERS

LEDs &  
INDICATORS

MINIATURE  
SWITCHES

LIMIT &  
SAFETY  
SWITCHES

CONTROL  
PRODUCTS

INTERFACE  
MODULES &  
SUPPORTS

RELAY  
BASES


DIN RAIL  
ENCLOSURES

BATTERIES

SOLAR  
PANELS

TRANS-  
FORMERS

## 5mm Pitch Pluggable Rising Clamp Terminal with Screw Flanges

- 2-20 pole solid block
- Pluggable male-female connectors
- Screw Flanges
- Horizontal female plug style
- Polarised mouldings
- Moulded in green UL94-V0 flame retardant PA
- Professional rising clamp terminals
- 0.2 to 4mm<sup>2</sup> (30 to 12 AWG)
- Anti solder wicking
- Captive screws
- Guided pin alignment
-  approved

### SPECIFICATION

Rating	20A/320V UL=12A/300V, VDE&IMQ=20A/320V
Dielectric strength	2kV
Impulse withstand voltage	4kV
Working temperature	-40°C to 110°C
Moulding	UL94-V0 flame retardant PA
Pin/terminal	Copper alloy, NI & SN
Rising clamp	Copper alloy, NI & SNM3 steel zinc
Screw/torque	plated, 0.5Nm
Recommended PCB hole size	ø1.5mm

### PCB mounting male horizontal

TYPE NO.	POLES	LENGTH	TYPE NO.	POLES	LENGTH
CTB9350/2FL	2	20mm	CTB9350/14FL	14	80mm
CTB9350/3FL	3	25mm	CTB9350/15FL	15	85mm
CTB9350/4FL	4	30mm	CTB9350/16FL	16	90mm
CTB9350/5FL	5	35mm	CTB9350/17FL	17	95mm
CTB9350/6FL	6	40mm	CTB9350/18FL	18	100mm
CTB9350/7FL	7	45mm	CTB9350/19FL	19	105mm
CTB9350/8FL	8	50mm	CTB9350/20FL	20	110mm
CTB9350/9FL	9	55mm			
CTB9350/10FL	10	60mm			
CTB9350/11FL	11	65mm			
CTB9350/12FL	12	70mm			
CTB9350/13FL	13	75mm			

CTB9350/ FL

