



12Vmax Impact Wrench CXT

TW141DZ

TW141D is a 12Vmax CXT cordless impact wrench of 12.7 mm (1/2") square drive,



TECHNICAL SPECIFICATIONS

Voltage	12 v
High Tensile Bolt	M6-M12
Standard Bolt	M8-M16
Vibration K factor	1.5 m/sec ²
Vibration: Fastening Bolt	7.5 m/sec ²
Noise sound pressure	93 dB(A)
Noise sound power	104 dB(A)
Noise K factor	3 dB(A)
Battery Type	Lithium-ion
Body only machine	✓
Net weight	1.1 - 1.2 kg
Nut Busting Torque	270 Nm
Driving Shank	1/2" Square
Impacts per Minute	0 - 3,200 ipm
No Load Speed	0 - 2,600 rpm
Max Fastening Torque	145 Nm

USER BENEFITS

- Electric brake
- Variable speed control by trigger
- Forward / reverse rotation
- LED job light
- Ergonomic soft grip
- Belt clip

[Link to product - www.makita.com](http://www.makita.com)



RELATED PRODUCTS

(Recon

■ OTHER