

14.4/18V Portable Fan LXT

DCF102Z

DCF102 is a cordless fan powered by 14.4 or 18V Lithium-ion battery.



TECHNICAL SPECIFICATIONS

| | |
|---|-------------------------------------|
| Air Flow (H/M/L) | 4.6 / 3.8 / 3.0 m ³ /min |
| Max Air Speed (Hi) | 180 m/min |
| Max Air Speed (Lo) | 120 m/min |
| Max Air Speed (Med) | 150 m/min |
| Run Time (4.0ah) with Oscillation (H/M/L) | 9.3 / 11.4 / 20.2 hrs |
| Battery Type | Lithium-ion |
| Body only machine | ✓ |
| Battery Range | 14.4 - 18 v |
| Diameter (D) | 180 mm |
| Net weight | 1.3 - 2.0 kg |

USER BENEFITS

- Compact size allows installation in confined spaces
- Automatic oscillation 45° Left / Right
- 3-Speed settings (Hi/Med/Low)
- Off-timer switch with 3 settings (1/2/4hrs) with LED display
- Adjustable fan head angle (up/down/left right)
- Adjustable hanging hook
- Screw hole for tripod mounting
- AC adaptor jack
- Release button for vertical angle adjustment of fan head

[Link to product - www.makita.com](http://www.makita.com)



RELATED PRODUCTS

(Recon

■ OTHER