

# 18V Metal Saw 150mm BL LXT

## DCS553ZJ

DCS553 is a 150mm (5-7/8") cordless metal cutter powered by 18V Li-ion battery.



### TECHNICAL SPECIFICATIONS

Battery Type	Lithium-ion
Body only machine	✓
Voltage	18 v
Blade Diameter	150 mm
Max Cut @ 0°	57.5 mm
Electric Brake	✓
Bore Diameter	20 mm
Joblight	✓
Noise sound pressure	103 dB(A)
Noise sound power	114 dB(A)
Noise K factor	3 dB(A)
No Load Speed	4,200 rpm
Vibration K factor	1.5 m/sec <sup>2</sup>
Vibration: Cutting Metal	2.5 m/sec <sup>2</sup>
Net weight	2.8 - 3.1 kg

### USER BENEFITS

- Automatic Torque Drive Technology: Automatically changes the cutting speed according to load condition for optimum operation
- Electric brake
- LED job light
- Brushless motor
- Soft start
- Retractable joist hook
- Built-in dust collection system
- Easy disposal – metal chip / dust can be thrown away by opening the cap of the dust box
- Stainless steel base plate
- Compact and lightweight design
- Flat motor housing end
- On-tool storage for hex wrench.
- Conveniently located shaft and lock for easy blade replacement
- Lock-off lever helps prevent accidental starts

Link to product - [www.makitauk.com](http://www.makitauk.com)



# RELATED PRODUCTS

(Recom

## ■ STANDARD ACCESSORIES

821551-8

MAKPAC CONNECTOR CASE (TYPE



## ■ OTHER