



18V Brushless Circular Saw 165mm DHS680Z

Model DHS680 is a 165mm (6-1/2") Cordless circular saw powered by 18V Li-ion battery.

18V Brushless Circular Saw 165mm



TECHNICAL SPECIFICATIONS

Battery Type	Lithium-ion
Body only machine	✓
Voltage	18 v
Battery quantity (4.0Ah)	0
Blade Diameter	165 mm
Max Cut @ 0°	57 mm
Max Cut @ 45°	41 mm
Max Cut @ 50°	37 mm
Bore Diameter	20 mm
Noise sound pressure	83 dB(A)
Noise sound power	94 dB(A)
Noise K factor	3 dB(A)
Maximum Output	680 w
No Load Speed	5,000 rpm
Vibration K factor	1.5 m/sec ²
Vibration: Cutting Wood	2.5 m/sec ²
Net weight	3.0 - 3.3 kg

USER BENEFITS

- Automatic Speed Control: Automatically changes the cutting speed according to load condition for optimum operation
- Electric brake
- Soft start
- Electronic current limiter for overload protection.
- Tool Hanger
- Twin LED job light
- Battery fuel gauge
- Rear dust exhaust port
- Large lock off lever.
- Compact and lightweight design
- Ergonomic soft grip
- Blower function to clear wood dust from cutting line.
- Larger base than current models for more stable operation

[Link to product - www.makita.com](http://www.makita.com)



RELATED PRODUCTS

(Recom

■ OTHER