

18v Slide Compound Mitre Saw

DLS713NZ

Cordless Slide Compound Mitre Saw with double sliding mechanism.



TECHNICAL SPECIFICATIONS

Battery Type	Lithium-ion
Voltage	18 v
Battery Quantity (3.0 Ah)	0
Body only machine	✓
Blade Diameter	190 mm
Bore Diameter	20 mm
No Load Speed	2200 rpm
Max bevel range	45 - 5 °
Max mitre range	45 - 57 °
Depth of Cut @ 90°	52 mm
Depth of Cut @ 45°	25 mm
Vibration K factor	1.5 m/sec ²
Vibration no load	2.5 m/sec ²
Net weight	12.7 kg

USER BENEFITS

- Ergonomic soft grip
- Electric brake

[Link to product - www.makita.com](http://www.makita.com)



RELATED PRODUCTS

(Recom

■ OTHER