



18Vx2 Cut-Off Saw 355mm BL LXT DLW140Z

Model DLW140 is a 355mm (14") Cordless Portable Cut-off Saw powered by two 18V Li-ion batteries in series.



TECHNICAL SPECIFICATIONS

| | |
|--------------------------|------------------------|
| Battery Type | Lithium-ion |
| Body only machine | ✓ |
| Voltage | 36 (18V x 2) v |
| Bore Diameter | 25.4 mm |
| Max Wheel Thickness | 3.0 mm |
| Noise sound pressure | 103 dB(A) |
| Noise sound power | 115 dB(A) |
| Noise K factor | 3 dB(A) |
| Max Wheel Diameter | 355 mm |
| Maximum Output | 1,300 w |
| No Load Speed | 3,800 rpm |
| Vibration K factor | 1.5 m/sec ² |
| Vibration: Cutting Metal | 2.5 m/sec ² |
| Net weight | 17.2 - 17.8 kg |

USER BENEFITS

- Brushless motor
- Tool-less adjustment of guide plate
- Tool-less wheel change
- Large spark guard
- Quick release vice.
- Pin locking device
- Electric brake
- Soft start
- Load status indicator: As the load on the motor increases, the number of illuminated LED's increases. When the motor is operated with excessive load, all LEDs on the load status indicator will blink.

Link to product - www.makita.com



RELATED PRODUCTS

(Recom

■ OTHER