

M Class Dust Extractor 30L

VC3012M

Wet and Dry M-Class Dust Extractor

240V machine with power take-off

110V without power take-off

Class M - Removes 99.9% of dust with Limit Value for occupational exposure > 0.1 mg/m³.

Suitable for processes involving mica, china clay, gypsum, wood dust, such as softwood and hardwood and silica dust, such as masonry, concrete.



TECHNICAL SPECIFICATIONS

Power take off wattage (240V)	1800 W
Dust Bag Capacity	23.5 litres
Max Sealed Suction	23-25 kPa
Tank Capacity	30 litres
Tank capacity Wet	19 litres
Noise sound pressure	59 dB(A)
Max Airflow	3.2 - 3.7 m ³ /min
Input Wattage 110v	1000 w
Input Wattage 240v	1200 w
Net weight	10.0 kg

USER BENEFITS

- Push and clean system: takes just seconds to clean the filter.
- Washable PET cartridge filter protects turbine by holding back fine dust and debris.
- Robust plastic container with 2 wheels and 2 castors for excellent stability and mobility
- The motor head design integrates an area for tool storage during use and transportation.
- Innovative hose storage solution with two clamps on the backside of the tool box
- Power cable storage with 3 fixation points on the motor head and tool box
- Floor nozzles and extension tubes can be fixed onto the body for convenient storage
- Automatic On/Off function: machine activates when a connected power tool is used. 240V only
- Lightweight plastic container
- Air flow sensor beeps when air flow is reduced by clogged filter, full tank etc.
- Approved for Dust Classes M in accordance with the EU standard.

Link to product - www.makitauk.com



RELATED PRODUCTS

(Recon

■ OTHER