

Multipole In-line Plug


pro-SIGNAL



Specifications

Connector Type	: Circular Industrial
Connector Body Material	: Plated Metal
Gender	: Plug
Contact Gender	: Pin
No. of Contacts	: 5
Contact Termination	: Solder
Contact Material	: Copper
Connector Mounting Orientation	: Cable
Mounting Type	: In-Line
Panel Cutout Diameter	: 15mm

Diagram



Dimensions : Millimetres

No.	Designation	Material	Plating
1	Screw	Fe	Ni
2	Cover	Cu	
3	Body	Zn	

Part Number Table

Description	Part Number
Multipole In-line Plug, 5 Way	PSG01597

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-SIGNAL is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands
 Farnell.com/exclusive-brands
 Element14.com/exclusive-brands

pro-SIGNAL