

# velleman®

## TLM10 TEST LEADS



### Specifications

- contents: 4 crocodile clips / 4 x 0.16" pins / 2 x 0.08" pins / 2 forks
- Ratings: max. 30V - max. 2A
- -: -
- length: 35"
- remark: blister