

## R18RT-0 | 18V Cordless Rotary Tool



- Powerful cordless rotary tool for sanding, grinding, polishing, engraving, sculpting and many more applications.
- Slimline pencil design and variable speed control provides fine control and use on a variety of materials.
- 91.5cm cable for flexible working in situ.
- Includes 33 accessories pack with on-board storage slots.
- Universal collet can be used with any brand of accessory.

	R18RT-0
Cable length [cm]	91.5
Charger included?	No
Collet capacity (mm)	3.2
No load speed (rpm)	4000 - 35000
No. of batteries supplied	0
Power	18V
Sound power level [dB(A)]	95.0
Sound power level uncertainty [dB(A)]	3
Sound pressure level (dB(A))	84.0
Sound pressure level uncertainty [dB(A)]	3
Standard equipment	Storage box containing 33 accessories: 1x wrench, 3x grinding wheels, 1x cutting mandrel, 4x cutting discs, 1x polishing mandrel, 4x polishing wheels, 1x polishing compound, 2x sanding drums, 12x sanding rings, 1x 3.2mm drill bit, 1x carbon fibre brush, 1x engraving bit, 1x high speed cutter
Supplied in	Recyclable Carton
Vibration Level Main Handle [m/s <sup>2</sup> ]	23.0
Vibration uncertainty [m/s <sup>2</sup> ]	1.5
Voltage (V)	18
Weight [without battery] [Kg]	1.3
Weight with battery pack (kg)	1.7