


Expression Home XP-2100

DATASHEET / BROCHURE



Save money, space and time with this 3-in-1 featuring Wi-Fi Direct, individual inks and mobile printing.

When you're looking for an affordable, stylish and easy-to-use printer, the XP-2100 is sure to tick all the boxes. It's also compact, produces clear and vibrant prints and is capable of mobile printing with Wi-Fi, Wi-Fi Direct and a range of compatible Epson apps.

Sleek and stylish 3-in-1

Don't let a printer impact your decor - our stylish and compact 3-in-1 printers are designed to integrate into the home. This affordable model efficiently uses your space combining printing, scanning and copying facilities in one unit.

Easy to use

Keep things simple – that's the mantra behind the XP-2100. It provides a range of essential features while being incredibly easy to use. It's also flexible with Wi-Fi for printing and scanning wirelessly around the home, and Wi-Fi Direct for printing without a wireless network.

Efficient & affordable


The 603 ink series provides a low-cost yet reliable printing solution. This four-colour ink set can print an array of documents with defined text and graphics. Each colour is supplied individually, so you only replace the colours you need.

Unleash smart devices

Print and scan from smart devices using Epson's free iPrint app¹. Feeling artistic? The Epson Creative Print app can print photos directly from Facebook, create custom greeting cards and stationery, and even turn photos into colouring book templates¹. Alternatively, Email Print makes it possible to print from almost anywhere in the world by simply emailing files to the printer¹.

KEY FEATURES

- **Stylish 3-in-1**
Save money, space and time
- **Mobile printing**
Freedom to print from almost anywhere¹
- **Individual inks**
Save money by only replacing the colour used
- **Wi-Fi & Wi-Fi Direct**
Wireless printing with or without a network
- **Compact**
Small and lightweight design



EPSON[®]
EXCEED YOUR VISION

PRODUCT SPECIFICATIONS

TECHNOLOGY

Printing Method	Epson Micro Piezo™ print head
Minimum Droplet Size	3 pl, With Variable-Sized Droplet Technology
Ink Technology	Pigment black and Dye colour Inks
Printing Resolution	5,760 x 1,440 dpi
Nozzle Configuration	180 Nozzles black, 59 Nozzles per colour

PRINT

Printing Speed ISO/IEC 24734	8 pages/min Monochrome, 4 pages/min Colour
Maximum Printing Speed	27 pages/min Monochrome (plain paper), 15 pages/min Colour (plain paper), 42 Seconds per 10 x 15 cm photo (Epson Premium Glossy Photo Paper)
Colours	Black, Cyan, Yellow, Magenta

For detailed information on printing speeds please visit <http://www.epson.eu/testing>.

SCAN

Scanning Resolution	1,200 dpi x 2,400 dpi (Horizontal x Vertical)
Scanner type	Contact image sensor (CIS)

PAPER / MEDIA HANDLING

Number of paper trays	1
Paper Formats	A4, A5, A6, B5, C6 (Envelope), DL (Envelope), No. 10 (Envelope), Letter Legal, 9 x 13 cm, 10 x 15 cm, 13 x 18 cm, 13 x 20 cm, 20 x 25 cm, 100 x 148 mm, 16:9
Duplex	Manual
Print Margin	0 mm top, 0 mm right, 0 mm bottom, 0 mm left (Wherever margin is defined. Otherwise 3mm top, left, right, bottom.)
Paper Tray Capacity	100 Sheets Standard, 20 Photo Sheets
Media Handling	Borderless print, Manual duplex

GENERAL

Energy Use	12 W (standalone copying, ISO/IEC 24712 pattern), 0.8 W (sleep mode), 4.6 W (Ready), 0.3 W (Power off)
Product dimensions	390 x 300 x 146 mm (Width x Depth x Height)
Product weight	4 kg
Compatible Operating Systems	Mac OS X 10.6.8 or later, Windows 10 (32/64 bit), Windows 7, Windows 8, Windows 8.1, Windows Vista (32/64 bit), Windows XP SP3 or later (32-bit), Windows XP Professional x64 Edition SP2
Included Software	Epson Easy Photo Print, Epson Scan 2
WLAN Security	WEP 64 Bit, WEP 128 Bit, WPA PSK (TKIP), WPA PSK (AES)
Mobile & Cloud printing services	Epson Connect (iPrint, Email Print, Remote Print Driver)
Colour	Black

OTHER FEATURES

Features	Red eye removal, Photo Enhance
----------	--------------------------------

OTHER

Warranty	12 months Carry in Optional warranty extension available
----------	-------------------------------------------------------------

LOGISTICS INFORMATION

SKU	C11CH02401
EAN code	8715946665559
Country of Origin	Thailand
Layer	9 Units
Layer Block	12 Units

For more information please contact:

Home users: 0343 90 37766
 Business users*: 0871 42 37766
 Republic of Ireland: 01 436 7742
 Or visit us at <https://www.epson.co.uk/contactus>
 * 10p per minute plus network extras.

Web: www.epson.co.uk
www.epson.ie

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners. Product information is subject to change without prior notice.
 Last extracted: 2019-09-16

Expression Home XP-2100

WHAT'S IN THE BOX

- Individual Ink Cartridges
- Software (CD)
- Setup guide
- Power cable
- Main unit
- Warranty document

INK CARTRIDGE COMPATIBILITY



INK YIELD DATA

	Starfish 603	Starfish 603XL
●	150 pages*	500 pages*
● ● ● ● ●	150 pages*	350 pages*

* Approx. page yield based on ISO/IEC 24711/24712 or ISO/IEC 29102/29103. Actual yield will vary depending on images printed and usage conditions. For more information visit <http://www.epson.eu/pageyield>

RECOMMENDED PAPER

Photo Paper
Glossy
Papier Photo
GLACE

20 Sheets
A4
150 g/m²
210 x 297 mm
99 x 112 cm

Photo Paper
Glossy

200 g/m²

Value GLOSSY
Photo Paper
Papier photo
GLACE économique

20 Sheets
4" x 6"
183 g/m²
102 x 152 mm / A4
254 x 127 mm

Value Glossy
Photo Paper

183 g/m²

1. – Epson iPrint and Epson Creative Print require a wireless connection and the Epson printing apps. Epson Email print and Epson Remote Print Driver require an internet connection. For more information, supported languages and devices, please visit www.epsonconnect.eu.

