

# WorkForce WF-110W

DATASHEET / BROCHURE



Print anywhere with Epson's smallest and lightest wireless A4 inkjet printer that can be charged on the go via USB.

For professionals needing to print on the go, Epson's A4 portable printer provides a high-quality solution. Small and light, this inkjet printer features an integrated battery, an LCD screen, Wi-Fi and Wi-Fi Direct connectivity, and compatibility with Google Cloud Print and Epson iPrint<sup>1</sup>. It's great for printing invoices, contracts and more without worrying about wires.

## Portable printing

The WF-110W is Epson's smallest and lightest wireless A4 inkjet printer. It measures just 309x154x61mm and weighs 1.6kg.

## Print without a power cable

An in-built battery gives you the power to print 50 pages, which can be topped up simply by recharging it via USB. For even more flexibility, an optional external battery can give you the power to print up to 410 pages<sup>2</sup>.

## Convenient

Print wirelessly with compatible solutions such as Google Cloud Print and Epson Connect. Use Epson iPrint<sup>1</sup> app for wireless printing from smartphones and tablets. It can even receive files to print from almost anywhere in the world via Epson Email Print<sup>1</sup>.

## High-quality prints

The quality of this printer is reflected in the quality of the printouts. In fact, it is the only portable printer that uses pigment inks for all colours for durable, smudge-free results.

## Efficient

The WF-110W delivers an ISO print speed of 7ppm in black and 4ppm in colour<sup>3</sup> and has an ink yield of up to 250 pages in black and 200 in colour<sup>4</sup>. With a 3.7cm LCD screen, it's easy to set-up a Wi-Fi connection without the need for a PC, and to check ink supply levels.

## KEY FEATURES

- **Portable printing**  
Lightweight, compact design
- **Rechargeable battery**  
Plug into any USB port or recharge with the bundled AC adaptor
- **Wi-Fi & Wi-Fi Direct**  
Print wirelessly wherever you are
- **Quality results**  
Pigment inks ensure top results
- **User-friendly**  
Hassle-free with simple set-up



## PRODUCT SPECIFICATIONS

### TECHNOLOGY

Printing Method	Epson Micro Piezo™ print head
Minimum Droplet Size	1.5 pl, With Variable-Sized Droplet Technology
Ink Technology	Pigment ink
Nozzle Configuration	180 Nozzles black, 59 Nozzles per colour
Application	Home
All-in-One Functions	Print

### PRINT

Printing Speed ISO/IEC 24734	7 pages/min Monochrome, 4 pages/min Colour
Printing Speed ISO/IEC 24734	4 pages/min monochrome, 2 pages/min colour (battery operated)
Maximum Printing Speed	14 pages/min Monochrome (plain paper), 11 pages/min Colour (plain paper)
Printing Resolution	5,760 x 1,440 dpi

For detailed information on printing speeds please visit <http://www.epson.eu/testing>.

### PAPER / MEDIA HANDLING

Paper Formats	A4, A5, A6, B5, C6 (Envelope), DL (Envelope), No. 10 (Envelope), Letter Legal, 10 x 15 cm, 13 x 18 cm
Duplex	No
Paper Tray Capacity	20 Sheets Standard, 20 Sheets maximum, 5 Photo Sheets
Number of paper trays	1

### CONNECTIVITY

Interfaces	USB 2.0 Micro-B, Wireless LAN IEEE 802.11b/g/n (WiFi 4), Wi-Fi Direct
Network Printing Protocols	IPP, LPD, Port 9100, WSD
Network Management Protocols	SNMP, HTTP, DHCP, APIPA, DDNS, mDNS, SLP, WSD, LLTD, Ping

### GENERAL

Energy Use	1.3 W (sleep mode), 11 W (printing), 4 W (Ready), 0.3 W (Power off)
Product dimensions	309 x 159 x 61 mm (Width x Depth x Height)
Product weight	1.6 kg
Noise Level	45 dB (A) according to ISO 9296
Compatible Operating Systems	Mac OS X 10.6.8 or later, Windows 10 (32/64 bit), Windows 7 (32/64 bit), Windows 8 (32/64 bit), Windows 8.1 (32/64 bit), Windows Server 2008 R2, Windows Server 2012 R2, Windows Server 2016, Windows Vista (32/64 bit), Windows XP SP3 or later (32-bit), Windows Server 2003 R2, Windows server 2003 SP2 or later, Windows XP Professional x64 Edition SP2

### ADDITIONAL FEATURES

LCD screen	Type: Colour, Diagonal: 3.7 cm
------------	--------------------------------

### OTHER

Warranty	12 months Carry in Optional warranty extension available
----------	---

## LOGISTICS INFORMATION

SKU	C11CH25401DA
EAN code	8715946670829
Country of Origin	Philippines

For more information please contact:

Home users: 0343 90 37766  
Business users\*: 0871 42 37766  
Republic of Ireland: 01 436 7742  
Or visit us at <https://www.epson.co.uk/contactus>  
\* 10p per minute plus network extras.

Web: [www.epson.co.uk](http://www.epson.co.uk)  
[www.epson.ie](http://www.epson.ie)

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners.  
Product information is subject to change without prior notice.  
Last extracted: 2019-11-07

## WorkForce WF-110W

### WHAT'S IN THE BOX

- 2x Maintenance box
- AC Adaptor
- Ink cartridges (1 black, 1 three-colour cartridge)
- Main unit
- Micro-USB cable

### INK CARTRIDGE COMPATIBILITY



### INK YIELD DATA



Globe 267

● 250 pages\*

● 200 pages\*

\* Approx. page yield based on ISO/IEC 24711/24712 or ISO/IEC 29102/29103. Actual yield will vary depending on images printed and usage conditions. For more information visit <http://www.epson.eu/pageyield>

1. Epson iPrint requires a wireless connection. Email print requires an internet connection. For more information, supported languages and devices, please visit [www.epsonconnect.eu](http://www.epsonconnect.eu)
2. When using additional external battery which can be purchased separately. (50 pages: built-in battery; 360 pages: additional battery).
3. Determined in accordance with ISO/IEC 24734 showing the average of ESAT from the Office Category Test for default simplex/duplex. For more information visit [www.epson.eu/testing](http://www.epson.eu/testing)
4. Approx. page yield based on ISO/IEC 24711/24712. Actual yield will vary depending on images printed and usage conditions. For more information visit [www.epson.eu/pageyield](http://www.epson.eu/pageyield)

**EPSON**®