

TCS 50W DIGITAL SOLDERING IRON

- Ergonomic handle
- Temperature controlled
- Digital display
- Easy button operated temperature adjustment
- Range adjustable from 200°C - 450°C
- Iron plated, nickel coated bit for long life
- Upto 30,000 operations tip life
- 9 replacement tips in range
- PVC cable fitted as standard



Replacement Bits - 1100 series



Safety Stand ST6A

SPECIFICATIONS

Voltage	230
Temperature	200°C - 450°C
Power	50W
Leakage current	5.0 μ A
Fitted bit	1100 (2.3mm)
Cable types	PVC
Cable Length	1.5 mtr
Plug	UK, EU
Dims (Tip to handle)	235mm

- Manufactured to Din EN 60335-2-45
- CE & EMC Low Voltage directive conformity
- Easy change shimmed bits