


VB RJ45 LaR -DB RJ45 FRNC green 1.0m



| | |
|--------------------|---|
| Part number | 09 48 858 7588 010 |
| Specification | VB RJ45 LaR -DB RJ45 FRNC green 1.0m |
| HARTING eCatalogue | https://b2b.harting.com/09488587588010 |

Identification

| | |
|--------------------------|---|
| Category | Cable assemblies |
| Series | RJ45 |
| Specification | Pre-assembled on both sides |
| Connector 1 | HARTING VarioBoot RJ45 Preferred directions left/right |
| Connector 2 | HARTING DualBoot RJ45 |
| Type of cable | Copper cable (round) |
| Description of the cable | Wiring 1:1 Flame retardant Halogen-free |

Version

| | |
|-----------------|-------------------|
| Cable length | 1 m |
| Number of cores | 8 |
| Core structure | 4x 2 Twisted Pair |

Technical characteristics

| | |
|--|--|
| Limiting temperature | -20 ... +60 °C unmoved 0 ... +60 °C moved |
| Degree of protection acc. to IEC 60529 | IP20 |
| Transmission characteristics | Cat. 6 _A Class E _A up to 500 MHz |



Pushing Performance

Technical characteristics

| | |
|-----------|------------|
| Data rate | 10 Mbit/s |
| | 100 Mbit/s |
| | 1 Gbit/s |
| | 2.5 Gbit/s |
| | 5 Gbit/s |
| | 10 Gbit/s |

Material properties

| | |
|------------------|-------------|
| Material (cable) | FRNC (LSZH) |
| Colour (cable) | Green |

Specifications and approvals

| | |
|----------------|------------------------------|
| Specifications | IEC 11801 |
| | IEC 61156-6 |
| | IEC 60332-1 Flame retardancy |
| | IEC 60754-2 Halogen freeness |
| | IEC 60754-2 Non corrosive |
| | IEC 61034 Low smoke |

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 1 |
| Country of origin | Czechia |
| European customs tariff number | 85444290 |
| eCl@ss | 27060390 Ready-made data cable (unspecified) |