

# ROLINE Cat.6A (Class EA) Keystone, RJ-45, STP, with shutter, Tool-free, silver

<b>Product No.</b>	21.17.0321
<b>Manufacturer</b>	VALUE
<b>Manufacturer No.</b>	21.17.0321
<b>EAN (single piece)</b>	7630049614642



**Tool-free**

**The low-cost solution for Cat.6A cabling for data rates up to 10Gbit/s!  
Cat.6A/Class EA Keystone jack for installation in a Keystone blank 19" patch panel module frame.**

- Toolless mounting - without using a LSA tool: cable wires are simply placed into the guides of Keystone module, the module is closed and compressed - the connection is ready for use
- Cat.6A Keystone Jack (Module) STP
- Fully shielded Housing(zinc alloy)
- 360 degree fully shielded
- Slim type
- With internal plastic shutter, black
- 180 degree cable entry
- Support PoE per IEEE 802.3af,PoE+ per IEEE 802.3at
- For cables with AWG 22-24 (0.45-0.65mm)
- For cables with OD: 5.0-8.5mm
- Colour code on the Keystone jacks based on the standard EIA/TIA 568 A & B
- Dimensions (L x W x H): 37.9×15.8×22.2mm

## Technical specifications

Manufacturer	VALUE
Product group	Connection technology TP
Product type	RJ45 Keystone Jack
Colour	silver
Shield type	Screened
Transfer quality	Cat6A / Class EA
Assignment	EIA/TIA 568A & 568B
Connection direction	Straight