


ROLINE Audio/Video System, HDMI, via Cat.6A, 4K@60Hz, 30m/45m

Product No. 14.01.3417
Manufacturer ROLINE
Manufacturer No. 14.01.3417

roline
Designed for Professionals



2160p
UHD-1

4K

3D
capable

The ROLINE HDMI A/V system transmits an HDMI signal from a source device like a DVD player, a PC/laptop or a console via Cat.6A cable to a display device like a TV, monitor or beamer/projector - with a resolution of up to 3840x2160 @60Hz (max. 30m) or 1920x1080 @60Hz (max. 45m)!

Audio / video transmission is via HDMI and CAT. 6a cable. Up to 4k (3840x2160) @60Hz at a distance of up to 30m can be achieved. At longer distances of up to 45m the resolution is reduced to Full HD (1920x1080) @60Hz.

- Transmits HDMI signals from source devices such as DVD players, PCs/laptops or consoles to a TV, monitor or beamer/projector.
- Resolution: 4k (3840x2160) @60Hz at up to 30m; Full HD (1920x1080) @60Hz at up to 45m
- HDCP compatible
- Supports 3D video transmission
- Black metal housing

Technical specifications

Manufacturer ROLINE

Product group Splitters and selectors

Product type	HDMI Extender
Colour	black
Scope of delivery	transmitter, receiver, 2 power supplies, manual
Interface	HDMI
Max. distance	45 m
Video input	HDMI
Video output	HDMI
Max. resolution	2160p
Max. resolution	3840 x 2160 @60Hz (4K, UHD-1)
Dimensions (HxWxD)	92 x 23 x 63 mm
Power supply unit	Wallmount socket
Power supply output	12VDC, 2A
Technical particularity	VGA / HDMI signal over WLAN or LAN