

RCBO Circuit Breakers

Single Pole, B Curve

pro-ELEC

RoHS
Compliant



Features

- Breaking capacity : 6kA
- Cable up to 25mm²
- Width : 17.6mm/module
- IEC61009, EN61009
- DIN Rail Mount

Part Number Table

Description	Part Number
RCBO Circuit Breaker, 1Pole, 6A, 230V AC	PEL00866
RCBO Circuit Breaker, 1Pole, 10A, 230V AC	PEL00867
RCBO Circuit Breaker, 1Pole, 16A, 230V AC	PEL00868
RCBO Circuit Breaker, 1Pole, 20A, 230V AC	PEL00869
RCBO Circuit Breaker, 1Pole, 25A, 230V AC	PEL00870
RCBO Circuit Breaker, 1Pole, 32A, 230V AC	PEL00871
RCBO Circuit Breaker, 1Pole, 40A, 230V AC	PEL00872

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-ELEC is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands
Farnell.com/exclusive-brands
Element14.com/exclusive-brands

pro-ELEC