



12W

VT-612RD 12W LED PREMIUM PANEL WITH SAMSUNG CHIP
COLORCODE:6400K ROUND

Lumens 1000	Beam Angle 120	Dimensions ?170x12mm
-----------------------	--------------------------	--------------------------------

White
SKU:714

5 YEARS
WARRANTY



SENSOR
COMPATIBLE



Technical Information

Instant Start:	0-100% lt1Sec	LED Chip Type:	SMD
Output Voltage:	DC:24-48V	IP Rating:	IP20
Watts:	12	Dimmable:	No
Lumens:	1000	Warranty (Years):	5
Shape:	Round	PF:	>0.6
Beam Angle:	120	CRI:	>80
Cutting Size:	?160mm	Operation Temperature:	-20°C to 45°C
Unit Color:	White	Input Power:	AC:85-265V,50/60Hz
Body Type:	Aluminium	Sensor Compatibility:	Yes
Long life:	20,000 Hours		

Features

- ✓ Contemporary & Elegant Design
- ✓ Highly Efficient LED Samsung Chip
- ✓ Easy to install - Plug & Play
- ✓ High-quality power driver ensures a reliable lifetime
- ✓ Controlled Glare rating values for comfortable commercial applications
- ✓ No Lead or Mercury content hence Environment-friendly
- ✓ Easy to install & Low Maintenance
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.325
Unit CBM	0.001366

Listing Details

EAN Code	3800157641708
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	1120

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER

70

COUNTRIES