



REAR CONTROL PANEL

HIGH CRI MULTIPLE COLOURS



2300
LUMEN



2-8H
RUNTIME



58M
RANGE



IP65
IP RATING


NEW CRI-2300 - RECHARGEABLE HIGH CRI INDUSTRIAL SITE LIGHT

- Super bright 2300 Lumen White COB LED
- High CRI 96+ 5 coloured COB LED
- CCT range: 2700K / 3500K / 4500K / 5500K / 6500K
- Dual power - rechargeable & mains
- Super tough aluminium structure
- Built in aluminium heat sink
- 180° adjustable stand/handle
- IP65 dust & water resistance
- IK07 shock resistance
- Multi-country mains charger included
- 3½ hour charge time

BATTERY 11.1v 4400mAh Li-Ion Rechargeable Battery

WEIGHT 1150g (without cable)

DIMENSION 74 x 224 x 199mm



REAR CONTROL PANEL



5M POWER/CHARGE CABLE