


KEMET, GT, EMI/RFI Filters, Noise Suppression, 250 VAC, 250 V, 10 A



Dimensions

L	84mm NOM
W	50.8mm NOM
H	39mm NOM
Lead	Screw Terminals

Packaging Specifications

Packaging:	Tray, Box
Packaging Quantity:	40
Weight:	260 g

General Information

Series:	GT
Style:	Metal Box
Description:	Noise Filters
RoHS:	Yes
Miscellaneous:	35 K Self-Temperature Rise Max
Lead:	Screw Terminals

Specifications

Voltage AC:	250 VAC
Ripple Current:	10 A (AC/DC)
Temperature Range:	-25/+55°C
Voltage:	250 VDC, 1500 VAC Withstanding Voltage 1 Min. Line to Ground
Leakage Current:	0.5 mA MAX (250 V 60 Hz)
Resistance:	300 MOhms MIN Insulation 500 VDC 1 Min. Line To Ground