


KEMET, LF, EMI/RFI Filters, Noise Suppression, 250 VAC, 250 V, 15 A



General Information	
Series:	LF
Style:	Metal Box
Description:	Metal Box
Features:	Small Current
RoHS:	Yes
Qualifications:	UL
Miscellaneous:	30 K Self-Temperature Rise Max
Lead:	Screw Terminals

Dimensions	
L	115mm NOM
W	57mm NOM
H	50mm NOM
Lead	Screw Terminals

Specifications	
Voltage AC:	250 VAC
Ripple Current:	15 A (AC/DC)
Rated Temperature:	55°C
Temperature Range:	-20/+55°C
Voltage:	250 VDC, 1500 VAC Withstanding Voltage 1 Min. Line to Ground
Leakage Current:	1 mA MAX (250 V 60 Hz)
Resistance:	300 MOhms MIN Insulation 500 VDC 1 Min. Line To Ground

Packaging Specifications	
Packaging:	Tray, Box
Packaging Quantity:	15
Weight:	620 g