


KEMET, LF, EMI/RFI Filters, Noise Suppression, 250 VAC, 250 V, 20 A



Dimensions	
L	160mm NOM
W	70mm NOM
H	60mm NOM
Lead	Screw Terminals

Packaging Specifications	
Packaging:	Tray, Box
Packaging Quantity:	12
Weight:	1.2 kg

General Information	
Series:	LF
Style:	Metal Box
Description:	Metal Box
RoHS:	Yes
Miscellaneous:	30 K Self-Temperature Rise Max
Lead:	Screw Terminals

Specifications	
Voltage AC:	250 VAC
Ripple Current:	20 A (AC/DC)
Rated Temperature:	55°C
Temperature Range:	-20/+55°C
Voltage:	250 VDC, 1500 VAC Withstanding Voltage 1 Min. Line to Ground
Leakage Current:	1 mA MAX (250 V 60 Hz)
Resistance:	300 MOhms MIN Insulation 500 VDC 1 Min. Line To Ground