


KEMET, LF, EMI/RFI Filters, Noise Suppression, 250 VAC, 250 V, 30 A



Dimensions

L	160mm NOM
W	70mm NOM
H	60mm NOM
Lead	Screw Terminals

Packaging Specifications

Packaging:	Tray, Box
Packaging Quantity:	12
Weight:	1.2 kg

General Information

Series:	LF
Style:	Metal Box
Description:	Metal Box
RoHS:	Yes
Miscellaneous:	30 K Self-Temperature Rise Max
Lead:	Screw Terminals

Specifications

Voltage AC:	250 VAC
Ripple Current:	30 A (AC/DC)
Rated Temperature:	55°C
Temperature Range:	-20/+55°C
Voltage:	250 VDC, 1500 VAC Withstanding Voltage 1 Min. Line to Ground
Leakage Current:	1 mA MAX (250 V 60 Hz)
Resistance:	300 MOhms MIN Insulation 500 VDC 1 Min. Line To Ground

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.