


KEMET, LF, EMI/RFI Filters, Noise Suppression, 250 VAC, 250 V, 40 A



Dimensions

L	210mm NOM
W	120mm NOM
H	75mm NOM
S	60mm NOM
L1	190mm NOM
L2	170mm NOM
W1	100mm NOM

Packaging Specifications

Packaging:	Tray, Box
Packaging Quantity:	5
Weight:	3.2 kg

General Information

Series:	LF
Style:	Metal Box
Description:	Metal Box
Features:	Large Current
RoHS:	Yes
Miscellaneous:	40 K Self-Temperature Rise Max

Specifications

Voltage AC:	250 VAC
Ripple Current:	40 A (AC/DC)
Rated Temperature:	45°C
Temperature Range:	-20/+45°C
Voltage:	250 VDC, 1500 VAC Withstanding Voltage 1 Min. Line to Ground
Leakage Current:	1 mA MAX (250 V 60 Hz)
Resistance:	300 MOhms MIN Insulation 500 VDC 1 Min. Line To Ground