


KEMET, LF, EMI/RFI Filters, Noise Suppression, 250 VAC, 250 V, 20 A



Dimensions

L	180mm NOM
W	150mm NOM
H	65mm NOM
S	60mm NOM
L1	170mm NOM
W1	135mm NOM
W2	120mm NOM
U	29mm NOM
I	35mm NOM

Packaging Specifications

Packaging:	Tray, Box
Packaging Quantity:	7
Weight:	2.3 kg

General Information

Series:	LF
Style:	Metal Box
Description:	Metal Box
Features:	Three-Phase
RoHS:	Yes
Miscellaneous:	30 K Self-Temperature Rise Max

Specifications

Voltage AC:	250 VAC
Ripple Current:	20 A (AC/DC)
Rated Temperature:	55°C
Temperature Range:	-20/+55°C
Voltage:	250 VDC, 1500 VAC Withstanding Voltage 1 Min. Line to Ground
Leakage Current:	1 mA MAX (250 V 60 Hz)
Resistance:	300 MOhms MIN Insulation 500 VDC 1 Min. Line To Ground