


KEMET, LF, EMI/RFI Filters, Noise Suppression, 250 VAC, 250 V, 30 A



**Dimensions**

<b>L</b>	180mm NOM
<b>W</b>	150mm NOM
<b>H</b>	65mm NOM
<b>S</b>	60mm NOM
<b>L1</b>	170mm NOM
<b>W1</b>	135mm NOM
<b>W2</b>	120mm NOM
<b>U</b>	29mm NOM
<b>I</b>	35mm NOM

**Packaging Specifications**

<b>Packaging:</b>	Tray, Box
<b>Packaging Quantity:</b>	7
<b>Weight:</b>	2.4 kg

**General Information**

<b>Series:</b>	LF
<b>Style:</b>	Metal Box
<b>Description:</b>	Metal Box
<b>Features:</b>	Three-Phase
<b>RoHS:</b>	Yes
<b>Miscellaneous:</b>	30 K Self-Temperature Rise Max

**Specifications**

<b>Voltage AC:</b>	250 VAC
<b>Ripple Current:</b>	30 A (AC/DC)
<b>Rated Temperature:</b>	55°C
<b>Temperature Range:</b>	-20/+55°C
<b>Voltage:</b>	250 VDC, 1500 VAC Withstanding Voltage 1 Min. Line to Ground
<b>Leakage Current:</b>	1 mA MAX (250 V 60 Hz)
<b>Resistance:</b>	300 MOhms MIN Insulation 500 VDC 1 Min. Line To Ground