


KEMET, RG, EMI/RFI Filters, Noise Suppression, 250 VAC, 250 V, 8 A



General Information	
Series:	RG
Style:	Metal Cylinder
Description:	Noise Filters
RoHS:	Yes
Qualifications:	UL, TUV
Miscellaneous:	55 K Self-Temperature Rise Max
Lead:	Threaded Studs M8

Dimensions	
D	50mm NOM
L	60mm NOM
LL	13mm NOM
L1	12mm NOM
Lead	Threaded Studs M8

Specifications	
Voltage AC:	250 VAC
Ripple Current:	8 A (AC/DC)
Temperature Range:	-25/+55°C
Voltage:	250 VDC, 1500 VAC Withstanding Voltage 1 Min. Line to Ground
Leakage Current:	1 mA MAX (250 V 60 Hz)
Resistance:	100 MOhms MIN Insulation 500 VDC 1 Min. Line To Ground

Packaging Specifications	
Packaging:	Tray, Box
Packaging Quantity:	25
Weight:	220 g