


KEMET, MA, EMI/RFI Filters, Noise Suppression, 250 VAC, 250 V, 1 A



Dimensions	
L	38mm NOM
W	30mm NOM
H	22.5mm NOM
LL	7mm MIN

Packaging Specifications	
Packaging:	Tray, Box
Packaging Quantity:	100
Weight:	30 g

General Information	
Series:	MA
Style:	Plastic Box
Description:	Noise Filters
RoHS:	Yes
Qualifications:	UL, CSA, TUV
Miscellaneous:	30 K Self-Temperature Rise Max

Specifications	
Voltage AC:	250 VAC
Ripple Current:	1 A (AC/DC)
Temperature Range:	-25/+55°C
Voltage:	250 VDC, 1500 VAC Withstanding Voltage 1 Min. Line to Ground
Leakage Current:	0.75 mA MAX (250 V 60 Hz)
Resistance:	300 MOhms MIN Insulation 500 VDC 1 Min. Line To Ground